

# 1/C AL 25kV 320 TRXLPE 133% SIMpull® PVC MV-105

Type MV-105 Single Conductor Aluminum, 320 Mils Tree Retardant Cross Linked Polyethylene (TRXLPE) 133% Insulation Level, Tape Shield, SIMpull Polyvinyl Chloride (PVC) Jacket, Rated UL




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
- Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
- Insulation:** 320 Mils Tree Retardant Cross Linked Polyethylene (TRXLPE) 133% Insulation Level,
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
- Overall Jacket:** Polyvinyl Chloride (PVC)

## APPLICATIONS AND FEATURES:

Southwire's 25KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

## SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- UL 1072 Medium-Voltage Power Cables
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

## SAMPLE PRINT LEGEND:

SOUTHWIRE SIMpull{R} POWER CABLE MASTER-DESIGN {UL} XXX AWG COMPACT AL.--- {ALUMAFLEX}{R} AA8176 XXX MILS XLP 25KV 133% INS LEVEL 25%TS MV-105 SUN. RES. {NESC} PAT www.patentSW.com



**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness <sup>1</sup>	Approx. OD	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size*
	AWG/Kcmil	inch	inch	inch	mil	inch	lb/1000ft	lb	inch	inch
TBA	1/0	0.336	1.014	1.074	80	1.254	771	634	15.0	3.5
TBA	2/0	0.376	1.053	1.113	80	1.293	745	799	15.5	4
674586	3/0	0.423	1.100	1.160	80	1.340	821	1007	16.1	4
TBA	4/0	0.475	1.152	1.212	80	1.392	888	1270	16.7	4
TBA	250	0.520	1.206	1.266	80	1.446	965	1500	17.4	4
TBA	350	0.616	1.302	1.362	80	1.542	1127	2100	18.5	5
TBA	500	0.736	1.422	1.482	80	1.662	1354	3000	19.9	5
TBA	750	0.908	1.625	1.685	110	1.925	1851	4500	23.1	6
TBA	1000	1.060	1.777	1.837	110	2.077	2204	6000	24.9	6

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Conduit size based on 3 phase 40% fill-factor without ground

<sup>1</sup> Comply with ICEA S-93-639 Appendix C for jacket thickness determination

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C <sup>†</sup>	Allowable Ampacity In Air 90/105°C <sup>‡</sup>
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0	0.168	0.211	0.075	0.052	0.568 + j0.329	0.212 + j0.052	3523	155/165	200/225
2/0	0.133	0.167	0.070	0.050	0.521 + j0.316	0.168 + j0.050	3653	175/190	230/260
3/0	0.105	0.132	0.065	0.048	0.482 + j0.301	0.133 + j0.048	3806	200/215	270/300
4/0	0.084	0.105	0.060	0.046	0.450 + j0.286	0.106 + j0.046	3976	230/245	310/345
250	0.071	0.089	0.057	0.045	0.429 + j0.272	0.090 + j0.045	4151	250/270	345/380
350	0.051	0.064	0.051	0.043	0.394 + j0.248	0.064 + j0.043	4464	305/330	430/475
500	0.035	0.045	0.045	0.040	0.363 + j0.223	0.046 + j0.040	4854	370/400	530/590
750	0.024	0.030	0.040	0.039	0.328 + j0.189	0.031 + j0.039	5514	455/490	685/765
1000	0.018	0.023	0.035	0.037	0.307 + j0.167	0.024 + j0.037	6009	525/565	825/920

\* Calculations are based on three cables triplexed / 5 mil 25 % over lapping copper tape shield Earth resistivity of 100 ohms-meter

<sup>†</sup> Ampacities are based on TABLE 310.60(C)(78) Detail 1. of the 2020 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

<sup>‡</sup> Ampacities are based on TABLE 310.60(C)(70) of the 2020 National Electrical Code (40°C Ambient Air Temperature)

